#### Beijing JiTai Tech Detection Device Co.,Ltd





#### W-20 Webster Hardness Tester



#### Introduction

Webster Hardness Tester is an instrument that can promptly on-site test the hardness of aluminum alloy material, including section bar, tubes, plates, aluminum parts, and hardness of other soft mental. It is such an instrument convenient in usage, with a simple "clamp" and direct result-reading, that it always receives good feedback of high efficiency and strong stability.

Webster Hardness Tester is the best choice for mechanical testing on aluminum alloy material, it is conform to Chinese nonferrous standard YS/T420-2004 and US standard ASTM B647-84(2000).

## **Using Scope**

Especially suitable in production site, sales site or construction site for quickly testing on bulk products with non-destructive quality inspection piece by piece.

Besides aluminum alloy material, it is also suitable to test red copper, brass, soft copper etc.

# **Application:**

- W-20: General Model, suitable for common aluminum materials;
- W-20A:Suitable for aluminum materials with thickness ≤13mm;
- W-20B:Suitable for aluminum tube with inner dia.≥6mm;
- W-B75:Suitable for brass tube, brass strip;
- W-BB75: Suitable for red copper tube, red copper strip;
- W-B92:Suitable for soft stainless steel, cold-rolled strip.

### **Advantages:**

 Indenter: Re-engineerred with advanced material and new production technology manufactured, higher hardness, long service life, good interchangeability;



### Beijing JiTai Tech Detection Device Co.,Ltd



- Indicator Hand: High strength indicator hand, less likely to be bent by long-term using or mis-operation;
- Dial Glass: High strength, high toughness, uneasy to be broken or scratched;
- Handle: Forged aluminum alloy handle with fine anodized finishing, high resistance to abraision and stain;
- Hardness Blocks: Tested by standard Rockwell hardness tester, attached with test report;
- Good Stability: Stable full scale point, stable calibration point, indicator never glides;
- Easy Conversion: Results can be converted to Vickers, Rockwell and Brinell.

### **Specification:**

Model	W-20
Testing Range	$0 \sim 20$ HW (equivalent to $20 \sim 110$ HRE,58-131HRV)
Resolution	0.5 HW (5 ~ 17 HW)
Repeatability	0.5 HW (5 ~17 HW)
Application	Aluminum Alloy
Suitable Specimen Size	Thickness 0.4-6 Inner Dia. >10mm
Dimension	31*22*10cm(L*W*H)
Packing Weight	2.0KG